








Screws

- TSPIC Ø5X min.35 DIN7505-A
- TSPIC M5X min.20 UNI 7688 DIN965
- TSPEI M5X min.20 UNI 5933 DIN7991
- TSPIT M5X min.20 UNI 6109 DIN963
- TSPIC M5X min.20 UNI 8113 DIN7500-M




Installation

Hinge centered on the door leaf



Hinge NOT centered on the door leaf



NOTE


Product info

For additional information view the website or product catalogue.

Certification

View product certifications in the catalogue or on the website.

⚠ Specific warnings



- Double the upper hinge whether a door closer is used;
- Double the bottom hinge whether a door stop or drop down seal is used;
- Place a central hinge whether the door leaf is higher than 2100 mm.



Scan me for view
website or
catalogue

Installation
examples



KK7MIDM01500 Rev 5 - 03 2024